





Disabled Persons Toilet Alarm Kit

Model: FIS-SA-Alarm

Version 1.0
July 2026 release

Disabled Persons Toilet Alarm Kit Model: FIS-SA-Alarm



Product Technical Specification

Disable Reset on main control panel (some local authorities require that the alarm can only be reset using the remote reset unit which is sited where the alarm is installed ensuring the alarm area is investigated to see if anyone is in need of help before unit is reset). Reset inactive label is supplied.

All buttons have Braille marking also the pull switch is fitted close to toilet /sink and the 2 pull handles are set as follows: Bottom handle 100mm above floor the second handle 800mm – 1000mm.

Rhinotek SINGLE ZONE DISABLED ALARM ASSISTANCE KIT


This disabled toilet single zone alarm kit allows a person in distress to raise an alarm and request assistance in the event of an emergency. The system is setup so that the Pull Cord and the Remote Reset & Indicator Panel are located next to the toilet in the disabled WC. The Main Control Panel is located in a staffed area, where it is both visible and audible to the responsible person on duty. When the alarm is activated, the staff member can press the "Call Answered" button to inform the person in distress that assistance is on the way. The LED indicator on the Remote Reset & Indicator Panel will become illuminated and tone/frequency of the alarm will decrease. The alarm can also be reset from the Remote Reset & Indicator Panel. The Over Door Indicator & Sounder can be installed over the door of the disabled WC to draw further attention to the location of the person in distress.

Safety an anti-ligature mechanism has been fitted in the pull cord to prevent possible accidents.

Any colour Buttons are available on request.

COMPLETE SINGLE ZONE KIT


Includes Main Control Panel, Remote Reset & Indicator Panel, Alarm Pull Cord Switch, Over Door Indicator & Sounder, Disabled WC Self-Adhesive label, Inactive Sticker (for disabling the RESET button) and M3.5 Socket screws.



Disabled Persons
Toilet Alarm Kit
Model: FIS-SA-Alarm

Specifications				
	Controller	Over door light	Reset point	Ring pull(white)
Power supply	220 ~ 240V AC 50Hz			
Output	12V DC			
Fuse	Internal thermal			
Alarm type	80dB			
Battery backup	Ni-MH PP3 9volt 250mAh			
Dimensions (mm) W x H x D	85 x 145 x 15	88 x 88 x 35	85 x 85 x 13	25 x 83 (diameter)
Cable requirements	4 or 6 core security alarm cable 7/0.2 or similar			
Back box requirements	35mm deep double gang, flush back box or 'round cornered' surface box	25mm deep single gang flush back box or 'round cornered' plastic surface box		Supplied with its own surfacemount enclosure

Disabled alarm kit layout





Gate 2, Aljada Logistics Area,
Behind Arada Project Management
Office, Near Airport Road,
Muweilah, 22436, Sharjah

rhinotek.ae

